

TRIPLE/S DYNAMICS, INC.
LAB REPORT

CONTACT: [REDACTED]

SALESMAN: [REDACTED]

SCREENING EVALUATION

EQUIPMENT USED: 1'x 3' TEXAS SHAKER® equipped with 3/8" woven wire (.105 W.D.) 57% open area

FEEDRATE: 35 TPH

Run #1 "6 ft. simulation" 200 lbs/min.

	<u>Wt.</u>	<u>%</u>
+3/8	121 lbs.	60
-3/8	83 lbs.	40

Run #2 "8 ft. simulation" 150 lbs/min.

	<u>Wt.</u>	<u>%</u>
+3/8	103 lbs.	65
-3/8	55 lbs.	35

Due to the small size of test unit, a 4 ft. simulation was not possible.

Bulk Density 78.51 lbs/ft³

Sieve Analysis attached.



T/SD Tech Services

